



Maxos TL-D, universal reflectors and optics

4MX092 1/2x58W RP WH

MAXOS R T8, 58 W

Maxos TL-D Universal reflectors are designed for electrical units holding 1 x TL-D lamp or, upon request, 2 x TL-D. Intended for applications in industry, supermarkets, shops and offices, they can be supplied with a white or silver outer finish. Mirror inlays create the following light distributions: wide beam (WB), medium beam (MB), narrow beam (NB) and asymmetrical beam (A). Maxos TL-D Universal reflectors can be ordered in IP20 and IP60 (lamp compartment only). IP60 applications require a PMMA or a polycarbonate cover. For IP20 applications, louvers (D6), prismatic screens (P) and acrylic micro-lens optics (MLO) are available. White steel louvers (L) are available for both IP20 and IP60.

Product data

| General Information | | | |
|--------------------------|-------------------------|---------------------------------|----------------------|
| Accessory color | White | Order product name | 4MX092 1/2x58W RP WH |
| Product family code | 4MX092 [MAXOS R T8] | Order code | 910699117126 |
| | | Numerator - Quantity Per Pack | 1 |
| | | Numerator - Packs per outer box | 6 |
| | | Material Nr. (12NC) | 910699117126 |
| | | Full product name | 4MX092 1/2x58W RP WH |
| | | EAN/UPC - Case | 4030732253159 |
| | | EAN/UPC - Product/Case | 4030732656400 |
| Operating and Electrical | | | |
| Power Consumption | 58 W | | |
| Approval and Application | | | |
| Ingress protection code | IP20 [Finger-protected] | | |
| Product Data | | | |
| Full product code | 403073265640099 | | |