



# Modena

## SGP681 CPO-T140W K EB II OC GB AL GR

MODENA P, MASTER CosmoWhite CPO-TW, 140 W, Electronic, Safety class II, Optic for CosmoPolis lamp, Glass bowl/cover, Grey

Modena is a road-lighting luminaire that combines elegance and excellent lighting performance. Its fluid, rounded form gives it a strong and distinctive visual character. Modena offers a wide choice of optical, electrical and mechanical options to satisfy all road applications. It allows considerable energy savings (dimming with standard dimming devices or stand-alone Lumistep and Chronosense systems; electronic ballast or Telemangement system) and is easy to install and maintain. The Modena family accommodates CosmoPolis white-light technology and LED-enabled versions and comes in three sizes – for mounting heights from 3.5 to 12 meters. Each Modena luminaire is fully recyclable; only the light source and driver have to be recycled separately.

### Product data



General Information	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]
Gear	EB [Electronic]
Product family code	SGP681 [MODENA P]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	0°
Number of light sources	1
Optical cover type	Glass bowl/cover

Optic type outdoor	Optic for CosmoPolis lamp
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	140 W
Mechanical and Housing	
Housing Color	Grey
Parts color	All parts colored
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II
Product Data	
Order product name	SGP681 CPO-T140W K EB II OC GB AL GR
Full product name	SGP681 CPO-T140W K EB II OC GB AL GR
Full product code	872790060538900
Order code	910722100109

Material Nr. (12NC)	910722100109
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900605389
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900605389

Dimensional drawing



Product
SGP681 CPO-T140W K EB II OC GB AL GR

