



EFix TCS260

GCS260 228 D6

EFix Surface mounted optics, 2, 28 W

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

Product data

General Information	
Product family code	GCS260 [EFix Surface mounted optics]
Value ladder	Performance
Light Technical	
Number of light sources	2
Operating and Electrical	
Power Consumption	28 W
Product Data	
Order product name	GCS260 228 D6

Full product name	GCS260 228 D6
Full product code	872790062519600
Order code	910925230611
Material Nr. (12NC)	910925230611
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900625196
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900625196