



Image
not yet
available

Mini 300 Cube DBP300

ZBP300 TB

IP WH

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Dane produktu

Informacje ogólne		Materiał Nr (12NC)	
Rodzina produktów	ZBP300 [IP WH]	Numerator - Quantity Per Pack	1
Dane techniczne produktu		EAN/UPC – Produkt/opakowanie	8718291041153
Nazwa produktu na zamówieniu	ZBP300 TB	Numerator - Packs per outer box	1
Pełna nazwa produktu	ZBP300 TB	EAN/UPC – Opakowanie	8718291041153
Full EOC	871829104115300		
Kod zamówienia	04115300		