



TCW060

TCW060 2xTL-D58W HFP EL1

TCW060, 2, MASTER TL-D, 58 W, HF Performer, Emergency lighting 1 hour duration

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data


General Information		Mechanical and Housing	
Lamp family code	TL-D [MASTER TL-D]	Fixation point length distance (Nom)	1,200 mm
Gear	HFP [HF Performer]	Housing Color	Grey
Service tag	Yes	Overall length	1,570 mm
Product family code	TCW060 [TCW060]	Approval and Application	
CE mark	Yes	Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Glow-wire test	Temperature 650 °C, duration 5 s	Mech. impact protection code	IK08 [5 J vandal-protected]
Light Technical		Application Conditions	
Number of light sources	2	Suitable for random switching	Yes
Optical cover type	Polycarbonate bowl/cover prismatic	Product Data	
Operating and Electrical		Order product name	TCW060 2xTL-D58W HFP EL1
Input Voltage	220 to 240 V	Full product name	TCW060 2xTL-D58W HFP EL1
Power Consumption	58 W	Full product code	871829103013300
Connection	Screw connection block 3-pole	Order code	03013300

TCW060

Material Nr. (12NC)	910925302712
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291030133
Numerator - Packs per outer box	1

EAN/UPC - Case	8718291030133
----------------	---------------

Dimensional drawing



Product	A	B
TCW060 2xTL-D58W HFP EL1	1,200 mm	1,570 mm

