



# Pacific Performer

## WT360C 2xTL5-49W/840 HFP C

Pacific Performer, 2, TL5, 49 W, 840 neutral white, HF Performer, High-gloss mirror

If you want to reduce your energy costs and join a growing number of companies doing their part for sustainability, then the Pacific Performer WT360C is for you. Featuring a fresh new design, this waterproof luminaire combines highly energy-efficient T5 lamp technology with a new reflector system offering excellent beam control. What's more, installation is quick and easy, thanks to the flexible ceiling brackets and smart end-caps. And because the light engine itself can be replaced, it will be possible to upgrade to LEDs in the future without having to change the entire luminaire.

### Product data


General Information		Operating and Electrical	
Lamp family code	TL5 [TL5]	Power Consumption	49 W
Gear	HFP [HF Performer]	Connection	-
Product family code	WT360C [Pacific Performer]	Mechanical and Housing	
CE mark	Yes	Fixation point length distance (Nom)	1,200 mm
Flammability mark	For mounting on normally flammable surfaces	Overall length	1,621 mm
ENEC mark	ENEC mark	Approval and Application	
Glow-wire test	Temperature 850 °C, duration 5 s	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light Technical		Mech. impact protection code	IK08 [5 J vandal-protected]
Number of light sources	2	Protection class IEC	Safety class I
Light source color	840 neutral white		
Optic type	High-gloss mirror		

Pacific Performer

Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	WT360C 2xTL5-49W/840 HFP C
Full product name	WT360C 2xTL5-49W/840 HFP C
Full product code	871829103089800
Order code	910925308912

Material Nr. (12NC)	910925308912
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291030898
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291030898

Dimensional drawing



Product	A	B	B	B	C
WT360C 2xTL5-49W/840 HFP C	1,600 mm	1,150 mm	1,200 mm	1,250 mm	1,621 mm

