



Metronomis LED Sharp

BDS660 GRN80-3S/740 PSR I MDA D9 76

Metronomis LED, LED GreenLine 8000 lm, Power supply unit with DALI interface, Metronomis distribution asymmetrical, Spigot for diameter 76 mm

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

Product data

General Information	
Lamp family code	GRN80 [LED GreenLine 8000 lm]
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Photocell	-
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018':

	statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source engine type	LED
Product family code	BDS660 [Metronomis LED]
Lighting Technology	LED
Value ladder	Specification

Metronomis LED Sharp

Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Std deviation colour matching	5
Upwards light output ratio	5
Luminous Flux	7,047 lm
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	99 lm/W
Colour rendering index (CRI)	>70
Light source colour	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	52° x 62°
Optic type outdoor	Metronomis distribution asymmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	55 W
Power Factor (Fraction)	0.96
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Polycarbonate

Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Spigot for diameter 76 mm
Optical cover/lens shape	-
Optical cover/lens finish	-
Overall height	990 mm
Overall diameter	560 mm
Effective projected area	0.4396 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge-protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

Product Data

Order product name	BDS660 GRN80-3S/740 PSR I MDA D9 76
Full product name	BDS660 GRN80-3S/740 PSR I MDA D9 76
Full EOC	871829188457600
Order code	88457600
Material no. (12 NC)	910925437929
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291884576
Numerator – packs per outer box	1
EAN/UPC – Case	8718291884576

Metronomis LED Sharp

Dimensional drawing

