



Iridium gen3 LED Medium

BGP382 LW10 GRN50/830 I DM CO GR SP

Iridium gen3 Medium, CityTouch with 10 years service contract, LED GreenLine 5000 lm, 830 warm white, Safety class I, Distribution medium, Grey, Spigot

Iridium gen3 is the first truly intelligent luminaire designed for seamless connectivity. No hassle in commissioning – just install the luminaire and control it from a distance through CityTouch management software. Remote light management made easy! The new ‘plug & play’ concept has been designed to ensure safe and easy installation in just three steps: 1. Install the spigot, 2. Plug in the mains, 3. Tilt and close the luminaire. The luminaire’s high efficiency at system level ensures significant energy savings compared to existing conventional installations, offering a fast payback. Thanks to its wide choice of lumen packages, optics and color temperatures, Iridium gen3 fits most applications in residential areas. The luminaire’s neo-classical design guarantees a consistent look and feel for your surroundings.

Product data

General Information			
Lamp family code	GRN50 [LED GreenLine 5000 lm]	there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Light source replaceable	Yes		
Number of gear units	1 unit		
Gear	EB [Electronic]	Light source engine type	LED
Driver included	Yes	Product family code	BGP382 [Iridium gen3 Medium]
Photocell	-	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires – January 2018”: statistically	Embedded control	-
		CE mark	Yes
		Warranty period	5 years

Iridium gen3 LED Medium

Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	No

Light Technical

Upward light output ratio	0
Luminous Flux	4,642 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	152°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	45 A
Inrush time	0.285 ms
Power Consumption	40 W
Power Factor (Fraction)	0.95
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	10

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	GPRS network
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey

Mounting device	Spigot
Optical cover shape	Flat
Optical cover finish	Textured
Overall length	650 mm
Overall width	330 mm
Overall height	157 mm
Effective projected area	0.031 m²
Dimensions (Height x Width x Depth)	157 x 330 x 650 mm
Parts color	Cover painted

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.41) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

Product Data

Order product name	BGP382 LW10 GRN50/830 I DM CO GR SP
Full product name	BGP382 LW10 GRN50/830 I DM CO GR SP
Full product code	871829191196800
Order code	910925438373
Material Nr. (12NC)	910925438373
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291911968
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291911968

Iridium gen3 LED Medium

Dimensional drawing

