



# Iridium gen3 LED Mini

BGP381 LW10 GRN25/830 II MSO CO GR SP

Iridium gen3 Mini, LED GreenLine 2500 lm, 830 warm white, Safety class II, Medium wide street optic, Grey, Spigot

Iridium gen3 is the first truly intelligent luminaire designed for seamless connectivity. No hassle in commissioning – just install the luminaire and control it from a distance through CityTouch management software. Remote light management made easy! The new ‘plug & play’ concept has been designed to ensure safe and easy installation in just three steps: 1. Install the spigot, 2. Plug in the mains, 3. Tilt and close the luminaire. The luminaire’s high efficiency at system level ensures significant energy savings compared to existing conventional installations, offering a fast payback. Thanks to its wide choice of lumen packages, optics and color temperatures, Iridium gen3 fits most applications in residential areas. The luminaire’s neo-classical design guarantees a consistent look and feel for your surroundings.

## Product data

General Information			
Lamp family code	GRN25 [LED GreenLine 2500 lm]	Light source engine type	LED
Light source replaceable	Yes	Product family code	BGP381 [Iridium gen3 Mini]
Number of gear units	1 unit	Lighting Technology	LED
Gear	EB [Electronic]	Embedded control	-
Driver included	Yes	CE mark	Yes
Photocell	-	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires – January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	-
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	No
		Light Technical	
		Upward light output ratio	0

## Iridium gen3 LED Mini

Luminous Flux	2,350 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	152°
Optic type outdoor	Medium wide street optic

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	20 W
Power Factor (Fraction)	0.96
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	20

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	GPRS network
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot
Optical cover shape	Flat
Optical cover finish	Textured

Overall length	531 mm
Overall width	273 mm
Overall height	156 mm
Effective projected area	0.024 m²
Dimensions (Height x Width x Depth)	156 x 273 x 531 mm
Parts color	Cover painted

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.41) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* L80	100000 h

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

### Product Data

Order product name	BGP381 LW10 GRN25/830 II MSO CO GR SP
Full product name	BGP381 LW10 GRN25/830 II MSO CO GR SP
Full product code	871869632115700
Order code	910925439287
Material Nr. (12NC)	910925439287
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696321157
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696321157

Iridium gen3 LED Mini

Dimensional drawing

