



# UniStreet

## BGS203 LED40/740 I DM DDF P1 C8K 32/48A

UniStreet Small, LED module 4000 lm, Distribution medium, DynaDimmer with fixed presets, Universal for diameter 32 to 48 mm adjustable

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customers who are preparing big renovation projects, TCO oriented

### Product data

General Information			
Lamp family code	LED40 [LED module 4000 lm]	extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source replaceable	Yes		
Number of gear units	1 unit	Light source engine type	LED
Driver included	Yes	Service tag	Yes
Photocell	NEMA socket for photocell	Product family code	BGS203 [UniStreet Small]
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At	Lighting Technology	LED
		Glow-wire test	Temperature 650 °C, duration 5 s
		Flammability mark	-
		CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	No

Embedded control	DynaDimmer with fixed presets
------------------	-------------------------------

#### Light Technical

Upward light output ratio	0
Luminous Flux	3,485 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	70
Number of light sources	2
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	154°
Optic type outdoor	Distribution medium

#### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	31.5 W
Power Factor (Fraction)	0.9
Connection	Screw connection block 3-pole
Cable	Cable 8.0 m without plug
Number of products on MCB of 16 A type 20 B	

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer
Control interface	Internal (no external connection)
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Tempered glass

Fixation material	Aluminum
Housing Color	Grey
Mounting device	Universal for diameter 32 to 48 mm adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	630 mm
Overall width	270 mm
Overall height	98 mm
Effective projected area	0.038 m²
Dimensions (Height x Width x Depth)	98 x 270 x 630 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L91

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Programmable

#### Product Data

Order product name	BGS203 LED40/740 I DM DDF P1 C8K 32/48A
Full product name	BGS203 LED40/740 I DM DDF P1 C8K 32/48A
Full product code	871869632128700
Order code	910925439301
Material Nr. (12NC)	910925439301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696321287
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696321287

Dimensional drawing

