



OptiFlood LED BVP506

BVP506 GRN107-3S/740 I DM GR T35

OptiFlood LED, LED GreenLine 10700 lm, Distribution medium

OptiFlood LED is a range of stylish, extremely efficient asymmetric floodlights that can be used to illuminate large areas. Designed around the latest LED technology, it offers significant energy and maintenance savings compared with conventional HID systems. Thanks to its highly efficient LEDGine area optics, it can be used for area lighting applications that have traditionally required HID-equivalent power levels. Integrated controls are available as an option, enabling additional energy savings. And LED upgrades can be easily incorporated, making this a truly future-proof solution. With its compact shape and aesthetically pleasing design, OptiFlood LED can be used in applications where design and appearance are just important as technical performance.

Product data

General Information			
Lamp family code	GRN107 [LED GreenLine 10700 lm]	median useful life (B50) value also represents the B10 value.	
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	Unit	Product family code	BVP506 [OptiFlood LED]
Driver included	Yes	Lighting Technology	LED
Photocell	-	Embedded control	-
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the		
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark
		EU RoHS compliant	Yes

OptiFlood LED BVP506

Light Technical	
Upwards light output ratio	0
Luminous Flux	9,149 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	113 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optical cover type	Clear glass
Luminaire light beam spread	73° x 26°
Optic type outdoor	Distribution medium
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	[delete] W
End CLO power consumption	[delete] W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	81 W
Power Factor (Fraction)	0.9
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	8
Temperature	
Ambient temperature range	-30 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	-

Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	730 mm
Overall width	460 mm
Overall height	176 mm
Effective projected area	0.1 m²
Dimensions (height x width x depth)	176 x 460 x 730 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Product Data	
Order product name	BVP506 GRN107-3S/740 I DM GR T35
Full product name	BVP506 GRN107-3S/740 I DM GR T35
Full EOC	871829141830600
Order code	41830600
Material no. (12 NC)	910925439406
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718291418306
Numerator – packs per outer box	1
EAN/UPC – Case	8718291418306

OptiFlood LED BVP506

Dimensional drawing

