



# OptiFlood LED BVP506

**BVP506 GRN68-3S/740 I A T35**

OptiFlood LED, LED GreenLine 6800 lm, Asymmetrical

OptiFlood LED is a range of stylish, extremely efficient asymmetric floodlights that can be used to illuminate large areas. Designed around the latest LED technology, it offers significant energy and maintenance savings compared with conventional HID systems. Thanks to its highly efficient LEDGine area optics, it can be used for area lighting applications that have traditionally required HID-equivalent power levels. Integrated controls are available as an option, enabling additional energy savings. And LED upgrades can be easily incorporated, making this a truly future-proof solution. With its compact shape and aesthetically pleasing design, OptiFlood LED can be used in applications where design and appearance are just important as technical performance.

## Product data

| General Information      |  |                          |   |
|--------------------------|--|--------------------------|---|
| Lamp family code         | GRN68 [LED GreenLine 6800 lm]  |                          | life (B50) value also represents the B10 value. |
| Light source replaceable | Yes  | Light source engine type | LED   |
| Number of gear units     | 1 unit   | Product family code      | BVP506 [OptiFlood LED]                          |
| Driver included          | Yes  | Lighting Technology      | LED   |
| Photocell                | -  | Flammability mark        | -   |
| Remarks                  | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful | CE mark                  | Yes   |
|                          |  | ENEC mark                | ENEC mark                                       |
|                          |  | Warranty period          | 5 years   |
|                          |  | EU RoHS compliant        | Yes   |
|                          |  | Embedded control         | -   |

# OptiFlood LED BVP506

|                                    |                   |
|------------------------------------|-------------------|
| <b>Light Technical</b>             |                   |
| Upward light output ratio          | 0                 |
| Luminous Flux                      | 6,019 lm          |
| Standard tilt angle posttop        | 0°                |
| Standard tilt angle side entry     | 0°                |
| Correlated Color Temperature (Nom) | 4000 K            |
| Luminous Efficacy (rated) (Nom)    | 116 lm/W          |
| Color rendering index (CRI)        | 70                |
| Number of light sources            | 48                |
| Light source color                 | 740 neutral white |
| Optical cover type                 | Clear glass       |
| Luminaire light beam spread        | 48° x 66°         |
| Optic type outdoor                 | Asymmetrical      |

|  |                 |
|--|-----------------|
| <b>Operating and Electrical</b>          |                 |
| Input Voltage                            | 220 to 240 V    |
| Line Frequency                           | 50 to 60 Hz     |
| Inrush current                           | 46 A            |
| Inrush time                              | 0.250 ms        |
| Power Consumption                        | 60 W            |
| Power Factor (Fraction)                  | 0.9             |
| Connection                               | Screw connector |
| Cable                                    | -               |
| Number of products on MCB of 16 A type B | 11              |

|                           |               |
|---------------------------|---------------|
| <b>Temperature</b>        |               |
| Ambient temperature range | -30 to +35 °C |

|                               |                              |
|-------------------------------|------------------------------|
| <b>Controls and Dimming</b>   |                              |
| Dimmable                      | No                           |
| Driver/power unit/transformer | Power supply unit regulating |
| Control interface             | -                            |
| Constant light output         | No                           |

|                               |               |
|-------------------------------|---------------|
| <b>Mechanical and Housing</b> |               |
| Housing Material              | Aluminum      |
| Reflector material            | Glass         |
| Optic material                | Polycarbonate |
| Optical cover material        | Glass         |
| Fixation material             | Aluminum      |
| Housing Color                 | Aluminum      |
| Mounting device               | -             |
| Optical cover shape           | Flat          |

|                                     |                    |
|-------------------------------------|--------------------|
| Optical cover finish                | Clear              |
| Overall length                      | 730 mm             |
| Overall width                       | 460 mm             |
| Overall height                      | 176 mm             |
| Effective projected area            | 0.1 m²             |
| Dimensions (Height x Width x Depth) | 176 x 460 x 730 mm |

|  |  |
|--|--|
| <b>Approval and Application</b>        |  |
| Ingress protection code                | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code           | IK09 [10 J]                                  |
| Surge Protection (Common/Differential) | 4/4 kV                                       |
| Protection class IEC                   | Safety class I                               |

|  |                      |
|--|----------------------|
| <b>Initial Performance (IEC Compliant)</b> |                      |
| Luminous flux tolerance                    | +/-7%                |
| Initial chromaticity                       | (0.38, 0.38) SDCM <5 |
| Power consumption tolerance                | +/-10%               |
| Init. Color Rendering Index Tolerance      | +/-2                 |

|  |      |
|--|------|
| <b>Over Time Performance (IEC Compliant)</b>             |      |
| Control gear failure rate at median useful life 100000 h | 10 % |
| Lumen maintenance at median useful life* 100000 h        | L80  |

|                                    |                |
|------------------------------------|----------------|
| <b>Application Conditions</b>      |                |
| Performance ambient temperature Tq | 25 °C          |
| Maximum dim level                  | Not applicable |

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Product Data</b>             |                             |
| Order product name              | BVP506 GRN68-3S/740 I A T35 |
| Full product name               | BVP506 GRN68-3S/740 I A T35 |
| Full product code               | 871829142224200             |
| Order code                      | 910925439437                |
| Material Nr. (12NC)             | 910925439437                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 8718291422242               |
| Numerator - Packs per outer box | 1                           |
| EAN/UPC - Case                  | 8718291422242               |

## OptiFlood LED BVP506

### Dimensional drawing

