



# UniStreet

## BGP204 LED70-4S/740 I DM50 D9 48/60A

UniStreet Large, LED module 7000 lm, 740 neutral white, Safety class I, Distribution medium, Universal for diameter 48 to 60 mm adjustable

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance.

### Product data

| General Information      |  |                                    |                                  |
|--------------------------|--|------------------------------------|----------------------------------|
| Lamp family code         | LED70 [LED module 7000 lm]   | Embedded control                   | -                                |
| Light source replaceable | Yes  | CE mark                            | Yes                              |
| Number of gear units     | 1 unit   | Warranty period                    | 5 years                          |
| Driver included          | Yes  | Flammability mark                  | -                                |
| Photocell                | -  | ENEC mark                          | ENEC mark                        |
| Remarks                  | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | Glow-wire test                     | Temperature 650 °C, duration 5 s |
|                          |  | EU RoHS compliant                  | No                               |
|                          |  | Light Technical                    |                                  |
| Light source engine type | LED  | Upward light output ratio          | 0                                |
| Product family code      | BGP204 [UniStreet Large]   | Luminous Flux                      | 6,090 lm                         |
| Lighting Technology      | LED  | Standard tilt angle posttop        | 0°                               |
|                          |  | Standard tilt angle side entry     | 0°                               |
|                          |  | Correlated Color Temperature (Nom) | 4000 K                           |
|                          |  | Luminous Efficacy (rated) (Nom)    | 147 lm/W                         |
|                          |  | Color rendering index (CRI)        | 70                               |

|                             |                     |
|-----------------------------|---------------------|
| Number of light sources     | 2                   |
| Light source color          | 740 neutral white   |
| Optical cover type          | Flat glass          |
| Luminaire light beam spread | 154°                |
| Optic type outdoor          | Distribution medium |

#### Operating and Electrical

|  |                               |
|--|-------------------------------|
| Input Voltage                            | 220-240 V                     |
| Line Frequency                           | 50 to 60 Hz                   |
| Inrush current                           | 46 A                          |
| Inrush time                              | 0.25 ms                       |
| Power Consumption                        | 41.5 W                        |
| Power Factor (Fraction)                  | 0.96                          |
| Connection                               | Screw connection block 3-pole |
| Cable                                    | -                             |
| Number of products on MCB of 16 A type B | 11                            |

#### Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

#### Controls and Dimming

|                               |                                       |
|-------------------------------|---------------------------------------|
| Dimmable                      | Yes                                   |
| Driver/power unit/transformer | Power supply unit with DALI interface |
| Control interface             | DALI                                  |
| Constant light output         | No                                    |

#### Mechanical and Housing

|                        |   |
|------------------------|---|
| Housing Material       | Aluminum die cast                             |
| Reflector material     | Polycarbonate                                 |
| Optic material         | Polycarbonate                                 |
| Optical cover material | Tempered glass                                |
| Fixation material      | Aluminum                                      |
| Housing Color          | Grey  |
| Mounting device        | Universal for diameter 48 to 60 mm adjustable |
| Optical cover shape    | Flat  |
| Optical cover finish   | Clear   |
| Overall length         | 755 mm  |

|                                     |                   |
|-------------------------------------|-------------------|
| Overall width                       | 355 mm            |
| Overall height                      | 98 mm             |
| Effective projected area            | 0.04 m²           |
| Dimensions (Height x Width x Depth) | 98 x 355 x 755 mm |

#### Approval and Application

|  |  |
|--|--|
| Ingress protection code                | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code           | IK08 [5 J vandal-protected]                  |
| Surge Protection (Common/Differential) | Philips standard surge protection level      |
| Protection class IEC                   | Safety class I                               |

#### Initial Performance (IEC Compliant)

|                                       |                        |
|---------------------------------------|------------------------|
| Luminous flux tolerance               | +/-7%                  |
| Initial chromaticity                  | (0.381, 0.379) SDCM <5 |
| Power consumption tolerance           | +/-10%                 |
| Init. Color Rendering Index Tolerance | +/-2                   |

#### Over Time Performance (IEC Compliant)

|  |      |
|--|------|
| Control gear failure rate at median useful life 100000 h | 10 % |
| Lumen maintenance at median useful life* 100000 h        | L94  |

#### Application Conditions

|                                    |       |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level                  | 10%   |

#### Product Data

|                                 |                                      |
|---------------------------------|--------------------------------------|
| Order product name              | BGP204 LED70-4S/740 I DM50 D9 48/60A |
| Full product name               | BGP204 LED70-4S/740 I DM50 D9 48/60A |
| Full product code               | 871869637233300                      |
| Order code                      | 37233300                             |
| Material Nr. (12NC)             | 910925452106                         |
| Numerator - Quantity Per Pack   | 1                                    |
| EAN/UPC - Product/Case          | 8718696372333                        |
| Numerator - Packs per outer box | 1                                    |
| EAN/UPC - Case                  | 8718696372333                        |

## Dimensional drawing

