



# UniStreet

## BGP204 LED120/740 II DW D9 48/60A

UniStreet Large, LED module 12000 lm, Distribution wide,  
Universal for diameter 48 to 60 mm adjustable

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customers who are preparing big renovation projects, TCO oriented

### Product data

General Information		Lighting Technology	
Lamp family code	LED120 [LED module 12000 lm]	Glow-wire test	Temperature 650 °C, duration 5 s
Light source replaceable	Yes	Flammability mark	-
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	ENEC mark	ENEC mark
Photocell	-	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	No
Light source engine type	LED	Embedded control	-
Product family code	BGP204 [UniStreet Large]	Light Technical	
		Upward light output ratio	0
		Luminous Flux	10,790 lm
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	98 lm/W
Color rendering index (CRI)	70
Number of light sources	6
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	154°
Optic type outdoor	Distribution wide

#### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	106 W
Power Factor (Fraction)	0.98
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	8

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Universal for diameter 48 to 60 mm adjustable

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	755 mm
Overall width	355 mm
Overall height	98 mm
Effective projected area	0.04 m²
Dimensions (Height x Width x Depth)	98 x 355 x 755 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* L92	100000 h

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

#### Product Data

Order product name	BGP204 LED120/740 II DW D9 48/60A
Full product name	BGP204 LED120/740 II DW D9 48/60A
Full product code	871869631918500
Order code	910925452266
Material Nr. (12NC)	910925452266
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696319185
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696319185

## Dimensional drawing

