



Mini 300 Cube DCP300

DCP300 CDM-TD150W E-EB S-WB WH

DCP300, MASTERColour CDM-TD, 150 W, Empty, prepared for electronic gear, Symmetrical wide beam

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Product data

General Information		Optical cover type	
Lamp family code	CDM-TD [MASTERColour CDM-TD]	Optic type outdoor	Flat glass
Gear	E-EB [Empty, prepared for electronic gear]		Symmetrical wide beam
Product family code	DCP300 [DCP300]	Operating and Electrical	
Flammability mark	For mounting on normally flammable surfaces	Input Voltage	220 to 240 V
CE mark	Yes	Power Consumption	150 W
ENEC mark	ENEC mark	Cable	-
Light Technical			
Number of light sources	1		

Mini 300 Cube DCP300

Mechanical and Housing	
Housing Color	White
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class I
Product Data	
Order product name	DCP300 CDM-TD150W E-EB S-WB WH

Full product name	DCP300 CDM-TD150W E-EB S-WB WH
Full product code	872790062486100
Order code	910925470403
Material Nr. (12NC)	910925470403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900624861
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900624861

Dimensional drawing

