



Mini 300 Cube DBP300

**DBP300 CDM-TD150W/942 IC 240V S-WB WH
MR**

DBP300, MASTERColour CDM-TD, 150 W, Symmetrical wide beam

In today's environment of continuous innovation, it's not often that a genuine breakthrough in technology is made. But that's exactly what the new Mini 300 is. Mini 300 is an innovation from Philips with the latest technology of optics that improves the efficiency of the total lighting system. It is suitable to be applied in various types of lighting installations, be it for indoor or outdoor applications. Here are more reasons why Mini 300 is amongst one of Philips' many best-in-class lighting solutions. Less energy consumption Mini 300's high efficiency even helps you save your operating and maintenance costs, resulting in a significantly lower cost of ownership. Excellent colour rendering Mini 300's unparalleled 'daylight' colour rendering of Ra 96 creates an inviting atmosphere. Compact design A smaller lamp means smaller housing and smaller cut out dimensions for a more compact, stylish installation. Enhanced safety Mini 300's specially engineered louvers shield people's eyes from the burner, reducing glare and allowing for clearer vision. More corporate identity With the high colour rendering and a colour temperature that creates a daylight impression (4,200K), people see your true corporate colours as you intended. More sparkle The Mini 300's minute burners are reflected on surfaces as tiny pinpoints of light, making things look brighter and cleaner. Easier cleaning Mini 300 is IP65, which means that it is well sealed, moreover it is jet and dust proof for easy hose spray cleaning. Many mounting possibilities The new Mini 300 can be recessed or surfacemounted in the canopy, or on poles and walls. Easy installation and maintenance It takes just one man and 10 minutes to install. Simply hang the luminaire with the provided mounting accessories, make the electrical connection, and swing the luminaire into its locking position. Couple this with Mini 300's outstanding light output ratio of up to 85% and you can

Mini 300 Cube DBP300

Product data

General Information	
Lamp family code	CDM-TD [MASTERColour CDM-TD]
Gear	CONV [Conventional]
Product family code	DBP300 [DBP300]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Light Technical	
Number of light sources	1
Light source color	942 neutral white
Optical cover type	Flat glass
Optic type outdoor	Symmetrical wide beam
Operating and Electrical	
Input Voltage	240 V
Power Consumption	150 W
Cable	-
Mechanical and Housing	
Housing Color	White

Mounting device	Frame for recessed mounting
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class I
Product Data	
Order product name	DBP300 CDM-TD150W/942 IC 240V S-WB WH MR
Full product name	DBP300 CDM-TD150W/942 IC 240V S-WB WH MR
Full product code	869065318089500
Order code	910925486912
Material Nr. (12NC)	910925486912
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8690653180895
Numerator - Packs per outer box	1
EAN/UPC - Case	8690653180895

Dimensional drawing

