



Mini 300 Cube DCP300

DCP300 CDM-TD150W/942 IC 230V S-WB SI

DCP300, MASTERColour CDM-TD, 150 W, Symmetrical wide beam

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Product data

General Information		Operating and Electrical	
Lamp family code	CDM-TD [MASTERColour CDM-TD]	Light source color	942 neutral white
Gear	CONV [Conventional]	Optical cover type	Flat glass
Product family code	DCP300 [DCP300]	Optic type outdoor	Symmetrical wide beam
Flammability mark	For mounting on normally flammable surfaces		
CE mark	Yes	Input Voltage	230 V
ENEC mark	ENEC mark	Power Consumption	150 W
		Cable	-
Light Technical			
Number of light sources	1		

Mini 300 Cube DCP300

Mechanical and Housing	
Housing Color	Silver
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class I
Product Data	
Order product name	DCP300 CDM-TD150W/942 IC 230V S-WB SI

Full product name	DCP300 CDM-TD150W/942 IC 230V S-WB SI
Full product code	869065338318000
Order code	910925489512
Material Nr. (12NC)	910925489512
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8690653383180
Numerator - Packs per outer box	1
EAN/UPC - Case	8690653383180

Dimensional drawing

