



Mini 300 Cube DGP300

DGP300 CDM-TD150W/942 IC 230V A-MB SI

DGP300, MASTERColour CDM-TD, 150 W, Fascio medio
asimmetrico

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a special optic coating, which reflects 97% of the light, and by the use of CDM-TD 4200 K lamps. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300), surface mounted (DCP300) and post/wall mounted (DGP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Dati del prodotto

Informazioni generali	
Codice famiglia lampada	CDM-TD [MASTERColour CDM-TD]
Unità elettrica/alimentatore	CONV [Reattore convenzionale]
Codice famiglia prodotto	DGP300 [DGP300]
Tier	Performance
Marchio CE	SI
Marchio di infiammabilità	Per montaggio su superfici normalmente infiammabili
Marchio ENEC	Marchio ENEC

Dati tecnici di illuminazione	
Colore sorgente luminosa	942 bianco neutro
Tipo copertura ottica	Vetro piano
Tipo di ottica aree esterne	Fascio medio asimmetrico
Funzionamento e parte elettrica	
Tensione in ingresso	230 V
Consumo energetico	150 W
Cavo	-

Mini 300 Cube DGP300

Meccanica e corpo

Colore alloggiamento	Argento
----------------------	---------

Approvazione e applicazione

e una gestione termica	IP65 [Protetto contro la penetrazione di polvere, protetto contro i getti d'acqua]
------------------------	--

Codice di protezione dagli impatti meccanici	IK09 [10 J]
--	-------------

Classe di protezione IEC:	Classe di isolamento I
---------------------------	------------------------

Dati del prodotto

Nome prodotto ordine	DGP300 CDM-TD150W/942 IC 230V A-MB SI
----------------------	---------------------------------------

Nome completo prodotto	DGP300 CDM-TD150W/942 IC 230V A-MB SI
------------------------	---------------------------------------

Full EOC	869065318104500
----------	-----------------

Codice d'ordine	18104500
-----------------	----------

Codice materiale (12NC)	910925491912
-------------------------	--------------

Codice locale	18104500
---------------	----------

Numeratore SAP - Quantità per confezione	1
--	---

EAN/UPC - Prodotto/scatola	8690653181045
----------------------------	---------------

Numeratore - Confezioni per scatola esterna	1
---	---

EAN/UPC - Case	8690653181045
----------------	---------------

Disegno tecnico

