



# Mini 300 Cube DGP300

## DGP300 CDM-TD150W/942 IC 240V A-MB SI

DGP300, MASTERColour CDM-TD, 150 W, Asymmetrical medium beam

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a special optic coating, which reflects 97% of the light, and by the use of CDM-TD 4200 K lamps. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with colour rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300), surface mounted (DCP300) and post/wall mounted (DGP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth).

### Product data

General Information	
Lamp family code	CDM-TD [MASTERColour CDM-TD]
Gear	CONV [Conventional]
Product family code	DGP300 [DGP300]
Value ladder	Performance
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Light Technical	
Light source colour	942 neutral white
Optical cover type	Flat glass

Optic type outdoor	Asymmetrical medium beam
Operating and Electrical	
Input Voltage	240 V
Power Consumption	150 W
Cable	-
Mechanical and Housing	
Housing Colour	Silver
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mini 300 Cube DGP300

Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class I
Product Data	
Order product name	DGP300 CDM-TD150W/942 IC 240V A-MB SI
Full product name	DGP300 CDM-TD150W/942 IC 240V A-MB SI
Full EOC	869065318106900
Order code	18106900

Material no. (12 NC)	910925492412
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8690653181069
Numerator – packs per outer box	1
EAN/UPC - Case	8690653181069

Dimensional drawing

