



EFix TCS260

TCS260 2x49W/830 HFD-T D6 ACL WH

EFix surface mounted, 2, 49 W, 830 warm white, HF DALI touch-switch dimming, Semi-high-gloss optic double parabolic, ActiLume, White

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

Product data

| General Information | | Light Technical | |
|---------------------|---|--------------------------|--|
| Lamp family code | TL5 [TL5] | Number of light sources | 2 |
| Gear | HFD-T [HF DALI touch-switch dimming] | Light source color | 830 warm white |
| Product family code | TCS260 [EFix surface mounted] | Optic type | Semi-high-gloss optic double parabolic |
| Value ladder | Performance | Optical cover type | - |
| Embedded control | ActiLume | Operating and Electrical | |
| CE mark | Yes | Input Voltage | 220 to 240 V |
| Flammability mark | For mounting on normally flammable surfaces | | |

EFix TCS260

| | |
|-------------------------------|-------------------------|
| Power Consumption | 49 W |
| Mechanical and Housing | |
| Housing Color | White |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Protection class IEC | Safety class I |
| Application Conditions | |
| Suitable for random switching | Not applicable |

| | |
|---------------------------------|----------------------------------|
| Product Data | |
| Order product name | TCS260 2x49W/830 HFD-T D6 ACL WH |
| Full product name | TCS260 2x49W/830 HFD-T D6 ACL WH |
| Full product code | 87279006227000 |
| Order code | 910925500812 |
| Material Nr. (12NC) | 910925500812 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8727900622270 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8727900622270 |

Dimensional drawing



| Product | A | B | C |
|----------------------------------|----------|--------|----------|
| TCS260 2x49W/830 HFD-T D6 ACL WH | 1,300 mm | 650 mm | 1,541 mm |

