



# EFix TPS262

## TPS262 2x35W/830 HFS MEP M6 SMT WH

EFix suspended mounted, 2, 35 W, 830 warm white, HF Standard, Matt optic double parabolic louver closed, White

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HFS [HF Standard]
Service tag	Yes
Product family code	TPS262 [EFix suspended mounted]
Embedded control	-
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark

Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Light source color	830 warm white
Optic type	Matt optic double parabolic louver closed
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V

EFix TPS262

Power Consumption	35 W
Cable	-

Mechanical and Housing

Housing Color	White
Overall length	1,541 mm

Approval and Application


Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I

Application Conditions

Suitable for random switching	Not applicable
-------------------------------	----------------

Product Data	
Order product name	TPS262 2x35W/830 HFS MEP M6 SMT WH
Full product name	TPS262 2x35W/830 HFS MEP M6 SMT WH
Full product code	872790063395500
Order code	910925516412
Material Nr. (12NC)	910925516412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900633955
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900633955

Dimensional drawing



Product	B	C
TPS262 2x35W/830 HFS MEP M6 SMT WH	650 mm	1,541 mm

