



TTX260

TTX261 2x49W/840 1x HFS C-NB PL5 WH

TTX260, 2, 49 W, 840 neutral white, 1 unit, HF Performer, High-gloss narrow beam, White

TTX260 is a value-for-money, versatile light-line solution – it can be used with or without (low-cost) reflectors, and the family easily covers most applications. This simple, two-component system features a clever design that avoids the use of a geartray. And T5 miniaturization minimizes the use of materials. These factors make TTX260 a low-cost investment, and yet its relatively high light output ratio ensures good lighting performance. What's more, installation costs are minimized thanks to the place-and-click fitting system, which requires no special tools or training. Sturdy, yet slim and stylish, TTX260 has a look similar to the popular Maxos light-lines.

Product data

General Information		Operating and Electrical	
Lamp family code	TL5 [TL5]	Power Consumption	49 W
Number of gear units	1 unit	Mechanical and Housing	
Gear	HFP [HF Performer]	Housing Color	White
Product family code	TTX261 [TTX260]	Approval and Application	
CE mark	Yes	Ingress protection code	IP20 [Finger-protected]
ENEC mark	ENEC mark	Protection class IEC	Safety class I
Glow-wire test	Temperature 850 °C, duration 5 s	Application Conditions	
Light Technical		Suitable for random switching	Not applicable
Number of light sources	2	Product Data	
Light source color	840 neutral white	Order product name	TTX261 2x49W/840 1x HFS C-NB PL5 WH
Optic type	High-gloss narrow beam		

TTX260

Full product name	TTX261 2x49W/840 1x HFS C-NB PL5 WH
Full product code	871829103469800
Order code	910925531812
Material Nr. (12NC)	910925531812
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8718291034698
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291034698

Dimensional drawing

