



TTX260

TTX261 1x49W/840 1x HFS C-A 5 WH

TTX260, 1, 49 W, HF Performer, High-gloss asymmetrical

TTX260 is a value-for-money, versatile light-line solution – it can be used with or without (low-cost) reflectors, and the family easily covers most applications. This simple, two-component system features a clever design that avoids the use of a geartray. And T5 miniaturization minimizes the use of materials. These factors make TTX260 a low-cost investment, and yet its relatively high light output ratio ensures good lighting performance. What's more, installation costs are minimized thanks to the place-and-click fitting system, which requires no special tools or training. Sturdy, yet slim and stylish, TTX260 has a look similar to the popular Maxos light-lines.

Product data

General Information		Mechanical and Housing	
Lamp family code	TL5 [TL5]	Housing Color	White
Number of gear units	1 unit		
Gear	HFP [HF Performer]	Approval and Application	
Product family code	TTX261 [TTX260]	Ingress protection code	IP20 [Finger-protected]
CE mark	Yes	Protection class IEC	Safety class I
ENEC mark	ENEC mark	Application Conditions	
Glow-wire test	Temperature 850 °C, duration 5 s	Suitable for random switching	Not applicable
Light Technical		Product Data	
Number of light sources	1	Order product name	TTX261 1x49W/840 1x HFS C-A 5 WH
Light source color	840 neutral white	Full product name	TTX261 1x49W/840 1x HFS C-A 5 WH
Optic type	High-gloss asymmetrical	Full product code	871829103512100
Operating and Electrical		Order code	910925536112
Power Consumption	49 W	Material Nr. (12NC)	910925536112
		Numerator - Quantity Per Pack	1

TTX260

EAN/UPC - Product/Case	8718291035121
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291035121

Dimensional drawing

