



# TTX260

## TTX260 4x49W/840 2x HFS C-MB PL7 SI

TTX260, 4, 49 W, 840 neutral white, 2 units, HF Performer, High-gloss medium beam, Silver

TTX260 is a value-for-money, versatile light-line solution – it can be used with or without (low-cost) reflectors, and the family easily covers most applications. This simple, two-component system features a clever design that avoids the use of a geartray. And T5 miniaturization minimizes the use of materials. These factors make TTX260 a low-cost investment, and yet its relatively high light output ratio ensures good lighting performance. What's more, installation costs are minimized thanks to the place-and-click fitting system, which requires no special tools or training. Sturdy, yet slim and stylish, TTX260 has a look similar to the popular Maxos light-lines.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Number of gear units	2 units
Gear	HFP [HF Performer]
Product family code	TTX260 [TTX260]
CE mark	Yes
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s

  

Light Technical	
Number of light sources	4
Light source color	840 neutral white
Optic type	High-gloss medium beam

Operating and Electrical	
Power Consumption	49 W

  

Mechanical and Housing	
Housing Color	Silver

  

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I

  

Application Conditions	
Suitable for random switching	Not applicable

  

Product Data	
Order product name	TTX260 4x49W/840 2x HFS C-MB PL7 SI

# TTX260

Full product name	TTX260 4x49W/840 2x HFS C-MB PL7 SI
Full product code	871829103743900
Order code	910925559212
Material Nr. (12NC)	910925559212
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8718291037439
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291037439

## Dimensional drawing

