



Mini 300 Cube DCP300

DCP300 CDM-TD70W/942 IC 230V S-WB WH

DCP300, MASTERColour CDM-TD, 70 W, Symmetrical wide beam

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Product data

| General Information | |
|-------------------------|---|
| Lamp family code | CDM-TD [MASTERColour CDM-TD] |
| Gear | CONV [Conventional] |
| Product family code | DCP300 [DCP300] |
| CE mark | Yes |
| Flammability mark | For mounting on normally flammable surfaces |
| ENEC mark | ENEC mark |
| Light Technical | |
| Number of light sources | 1 |

| Light source color | 942 neutral white |
|--------------------------|-----------------------|
| Optical cover type | Flat glass |
| Optic type outdoor | Symmetrical wide beam |
| Operating and Electrical | |
| Input Voltage | 230 V |
| Power Consumption | 70 W |
| Cable | - |

Mini 300 Cube DCP300

| | |
|------------------------------|--|
| Mechanical and Housing | |
| Housing Color | White |
| Approval and Application | |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK09 [10 J] |
| Protection class IEC | Safety class I |
| Product Data | |
| Order product name | DCP300 CDM-TD70W/942 IC 230V S-WB WH |

| | |
|---------------------------------|--------------------------------------|
| Full product name | DCP300 CDM-TD70W/942 IC 230V S-WB WH |
| Full product code | 869065338319700 |
| Order code | 38319700 |
| Material Nr. (12NC) | 910925602812 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8690653383197 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8690653383197 |

Dimensional drawing

