



Mini 300 Cube DCP300

DCP300 CDM-TD70W/830 IC 230V S-WB WH

DCP300, MASTERColour CDM-TD, 70 W, Symetryczna szeroki rozsył światła

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a patented optic coating (which reflects 97% of the light) and by use of e.g. the CDM-TD 150 W 4200 K lamp. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300) and surface mounted (DCP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Dane produktu

Informacje ogólne	
Kod rodziny lamp	CDM-TD [MASTERColour CDM-TD]
Osprzęt	CONV [Konwencjonalny]
Rodzina produktów	DCP300 [DCP300]
Znak CE	Tak
Oznaczenie palności	Do montażu na powierzchniach o normalnym poziomie palności
Oznaczenie ENEC	Znak ENEC

Dane techniczne oświetlenia	
Barwa źródła światła	830 barwa ciepło-biała
Typ klosza	Szyba płaska
Typ optyki na zewnątrz	Symetryczna szeroki rozsył światła
Eksploatacja i połączenie elektryczne	
Napięcie wejściowe	230 V
Zużycie energii	70 W
Przewód	-

Mini 300 Cube DCP300

Mechanika i korpus

Kolor Korpusu	Biel
---------------	------

Certyfikaty i zastosowania

Kod stopnia ochrony	IP65 [Zabezpieczone przed przenikaniem kurzu, strugoodporne]
---------------------	--

Mech. kod ochrony przed uderzeniami	IK09 [10 J]
-------------------------------------	-------------

Klasa ochrony IEC	Klasa bezpieczeństwa I
-------------------	------------------------

Dane techniczne produktu

Nazwa produktu na zamówieniu	DCP300 CDM-TD70W/830 IC 230V S-WB WH
------------------------------	--------------------------------------

Pełna nazwa produktu	DCP300 CDM-TD70W/830 IC 230V S-WB WH
Full EOC	872790062638400
Kod zamówienia	62638400
Materiał Nr (12NC)	910925603212
Numerator - Quantity Per Pack	1
EAN/UPC - Produkt/opakowanie	8727900626384
Numerator - Packs per outer box	1
EAN/UPC - Opakowanie	8727900626384

Rysunki techniczne

