



CoreLine Trunking

LL121X LED45S/840 1x PSD DA20 9 WH

CoreLine Trunking, LED Module, system flux 4500 lm, Power supply unit with DALI interface, Double asymmetric optic 20°

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information		Light Technical	
Lamp family code	LED45S [LED Module, system flux 4500 lm]	Luminous Flux	4,500 lm
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	141 lm/W
Driver included	Yes	Color rendering index (CRI)	≥80
Feed-through wiring	Feed-through wiring 9-phase	Number of light sources	3
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Beam angle of light source	120 degree(s)
Product family code	LL121X [CoreLine Trunking]	Light source color	840 neutral white
Lighting Technology	LED	Optic type	Double asymmetric optic 20°
Glow-wire test	Temperature 650 °C, duration 5 s	Optical cover type	-
Flammability mark	For mounting on normally flammable surfaces	Luminaire light beam spread	86° x 80°
		Unified glare rating CEN	Not applicable
		CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	3 years
		EU RoHS compliant	Yes

CoreLine Trunking

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.275 ms
Power Consumption	32 W
Power Factor (Fraction)	0.95
Connection	Connection unit 9-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover material	Acrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,730 mm
Overall width	95 mm
Overall height	52 mm
Dimensions (Height x Width x Depth)	52 x 95 x 1730 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data


Order product name	LL121X LED45S/840 1x PSD DA20 9 WH
Full product name	LL121X LED45S/840 1x PSD DA20 9 WH
Full product code	871829190737400
Order code	910925683011
Material Nr. (12NC)	910925683011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291907374
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291907374

Dimensional drawing




CoreLine Trunking


Dimensional drawing



Product	A
LL121X LED45S/840 1x PSD DA20 9 WH	1,725 mm



Product	A
LL121X LED45S/840 1x PSD DA20 9 WH	1,739 mm



Product	A
LL121X LED45S/840 1x PSD DA20 9 WH	1,999 mm

