



# High Power GearUnits

## ECB330 2xHPI-TP400W 230-240V PA FU

GearUnits, 2, MASTER HPI-T Plus, 400 W, 986 W, 230 to 240 V, Fuse included

Philips is one of the few companies able to provide total floodlight system solutions comprising all necessary elements – floodlight, lamp source and control gear unit. Our innovative high-power GearUnits are designed to meet our customers' need for a compact gear solution that is completely ready for installation. The pre-wired high-power control gear units are intended for use in combination with floodlights that are suitable for high-wattage HID lamps and cannot integrate electrical components because of limited space or high temperatures. A gear unit contains all electrical components (ballast, ignitors, capacitors), wiring and terminal blocks needed to ensure initial lamp ignition and proper operation of the lamp in stabilized current. The electromagnetic high-power GearUnits are available in both IP20 (ECB330) and IP65 (ECP330) versions. Within the GearUnits family there is also an electronic flicker-free ballast version (ECM330) available in IP20, which is suitable for the MVF403 MHN-LA 1000 W and MVF404 MHN-SE HO 2000 W ArenaVision floodlights. The ArenaVision floodlight family is specially designed for TV broadcasts from indoor and outdoor sports facilities. Electronic-ballast GearUnits completely eliminate the flicker effect, thereby guaranteeing perfect images filmed with super-slow-motion cameras.

### Product data

General Information		Flammability mark	
Lamp family code	HPI-TP [MASTER HPI-T Plus]	For mounting on normally flammable surfaces	
Number of gear units	2 units	ENEC mark	
Gear	CONV [Conventional]	-	
Product family code	ECB330 [GearUnits]	Light Technical	
Value ladder	Performance	Number of light sources	
CE mark	Yes	2	

## High Power GearUnits

### Operating and Electrical

Input Voltage	230 to 240 V
Line Frequency	50 Hz
Power Consumption	400 986 W
Connection	Screw connection block 3-pole

### Temperature

Ambient temperature range	-30 to +55 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
----------	----

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Energy Efficiency Index	A3
-------------------------	----

### Product Data

Order product name	ECB330 2xHPI-TP400W 230-240V PA FU
Full product name	ECB330 2xHPI-TP400W 230-240V PA FU
Full product code	871829106266000
Order code	06266000
Material Nr. (12NC)	910925725012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291062660
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291062660

## Dimensional drawing

