




# High Power GearUnits

## ECB330 MHN-FC1000W 230-240V FU

GearUnits, MASTER MHN-FC, 1000 W, 1110 W

Philips is one of the few companies able to provide total floodlight system solutions comprising all necessary elements – floodlight, lamp source and control gear unit. Our innovative high-power GearUnits are designed to meet our customers' need for a compact gear solution that is completely ready for installation. The pre-wired high-power control gear units are intended for use in combination with floodlights that are suitable for high-wattage HID lamps and cannot integrate electrical components because of limited space or high temperatures. A gear unit contains all electrical components (ballast, ignitors, capacitors), wiring and terminal blocks needed to ensure initial lamp ignition and proper operation of the lamp in stabilized current. The electromagnetic high-power GearUnits are available in both IP20 (ECB330) and IP65 (ECP330) versions. Within the GearUnits family there is also an electronic flicker-free ballast version (ECM330) available in IP20, which is suitable for the MVF403 MHN-LA 1000 W and MVF404 MHN-SE HO 2000 W ArenaVision floodlights. The ArenaVision floodlight family is specially designed for TV broadcasts from indoor and outdoor sports facilities. Electronic-ballast GearUnits completely eliminate the flicker effect, thereby guaranteeing perfect images filmed with super-slow-motion cameras.

### Product data

| General Information     |                                             | Value ladder             | Performance |
|-------------------------|---------------------------------------------|--------------------------|-------------|
| Lamp family code        | MHN-FC [MASTER MHN-FC]                      |                          |             |
| Number of gear units    | 1 unit                                      |                          |             |
| Gear                    | CONV [Conventional]                         |                          |             |
| Product family code     | ECB330 [GearUnits]                          |                          |             |
| Flammability mark       | For mounting on normally flammable surfaces |                          |             |
| CE mark                 | Yes                                         |                          |             |
| ENEC mark               | -                                           |                          |             |
| Light Technical         |                                             | Operating and Electrical |             |
| Number of light sources |                                             | 1                        |             |
| Input Voltage           |                                             | 230 to 240 V             |             |
| Line Frequency          |                                             | 50 Hz                    |             |

## High Power GearUnits

|                                 |                               |
|---------------------------------|-------------------------------|
| Power Consumption               | 1,000 1,110 W                 |
| Connection                      | Screw connection block 3-pole |
| <b>Temperature</b>              |                               |
| Ambient temperature range       | -30 to +55 °C                 |
| <b>Controls and Dimming</b>     |                               |
| Dimmable                        | No                            |
| <b>Approval and Application</b> |                               |
| Ingress protection code         | IP20 [Finger-protected]       |
| Energy Efficiency Index         | A3                            |

|                                 |                                |
|---------------------------------|--------------------------------|
| <b>Product Data</b>             |                                |
| Order product name              | ECB330 MHN-FC1000W 230-240V FU |
| Full product name               | ECB330 MHN-FC1000W 230-240V FU |
| Full product code               | 871829106270700                |
| Order code                      | 910925725412                   |
| Material Nr. (12NC)             | 910925725412                   |
| Numerator - Quantity Per Pack   | 1                              |
| EAN/UPC - Product/Case          | 8718291062707                  |
| Numerator - Packs per outer box | 1                              |
| EAN/UPC - Case                  | 8718291062707                  |

### Dimensional drawing

