



Selenium

SGP340 CPO-TW90W K EBR I OR FG LS-6 P1 4

SELENIUM, MASTER CosmoWhite CPO-TW, 90 W, Electronic regulating, Safety class I, Open CT-POT, Flat glass, LumiStep dimming 6 hours, Universal for diameter 48 to 60 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).


Product data

General Information		Optic type outdoor	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Open CT-POT	
Cap base	PGZ12 [PGZ12]	Operating and Electrical	
Gear	EBR [Electronic regulating]	Input Voltage	220 to 240 V
Photocell	NEMA socket for photocell	Power Consumption	90 W
Product family code	SGP340 [SELENIUM]	Mechanical and Housing	
Embedded control	LumiStep dimming 6 hours	Housing Colour	Grey
CE mark	Yes	Mounting device	Universal for diameter 48 to 60 mm
ENEC mark	-	Overall height	232 mm
Light Technical		Approval and Application	
Standard tilt angle post-top	5°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Standard tilt angle side entry	0°	Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Flat glass		

Protection class IEC	Safety class I
Product Data	
Order product name	SGP340 CPO-TW90W K EBR I OR FG LS-6 P1 4
Full product name	SGP340 CPO-TW90W K EBR I OR FG LS-6 P1 4
Full EOC	872790062935400
Order code	62935400

Material no. (12 NC)	910925801712
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900629354
Numerator – packs per outer box	1
EAN/UPC – Case	8727900629354

Dimensional drawing



Product
SGP340 CPO-TW90W K EBR I OR FG LS-6 P1 4

