



# Selenium

## SGP340 CDO-TT70W K II OR PC SKD 48/60

SELENIUM, MASTER CityWhite CDO-TT, 70 W, Safety class II, Open CT-POT, Polycarbonate bowl/cover, Universal for diameter 48 to 60 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).


### Product data

|                                |                                  |                                 |  |
|--------------------------------|----------------------------------|---------------------------------|--|
| <b>General Information</b>     |                                  | <b>Optic type outdoor</b>       |  |
| Lamp family code               | CDO-TT [MASTER CityWhite CDO-TT] | Open CT-POT                     |  |
| Cap-Base                       | E27 [E27]                        | <b>Operating and Electrical</b> |  |
| Gear                           | CONV [Conventional]              | Input Voltage                   | 230 to 240 V                                 |
| Photocell                      | -                                | Power Consumption               | 70 W   |
| Product family code            | SGP340 [SELENIUM]                | <b>Mechanical and Housing</b>   |  |
| Embedded control               | -                                | Housing Color                   | Gray   |
| CE mark                        | Yes                              | Mounting device                 | Universal for diameter 48 to 60 mm           |
| ENEC mark                      | -                                | Overall height                  | 268 mm                                       |
| <b>Light Technical</b>         |                                  | <b>Approval and Application</b> |  |
| Standard tilt angle posttop    | 5°                               | Ingress protection code         | IP66 [Dust penetration-protected, jet-proof] |
| Standard tilt angle side entry | 0°                               | Mech. impact protection code    | IK08 [5 J vandal-protected]                  |
| Number of light sources        | 1                                |                                 |  |
| Optical cover type             | Polycarbonate bowl/cover         |                                 |  |

|                      |                                       |
|----------------------|---------------------------------------|
| Protection class IEC | Safety class II                       |
| <b>Product Data</b>  |                                       |
| Order product name   | SGP340 CDO-TT70W K II OR PC SKD 48/60 |
| Full product name    | SGP340 CDO-TT70W K II OR PC SKD 48/60 |
| Full product code    | 872790063276700                       |
| Order code           | 63276700                              |

|                                 |               |
|---------------------------------|---------------|
| Material Nr. (12NC)             | 910925807312  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8727900632767 |
| Numerator - Packs per outer box | 1             |
| EAN/UPC - Case                  | 8727900632767 |

Dimensional drawing



|                                       |
|---------------------------------------|
| <b>Product</b>                        |
| SGP340 CDO-TT70W K II OR PC SKD 48/60 |

