



TMS028

TMS028 2xTL-D36W HF

TMS028, 2, MASTER TL-D, 36 W, Electronic high-frequency

TMS028 is a basic batten for 1 or 2 TL-D fluorescent lamps and includes optics for general lighting. It can be suspended or surface-mounted. A lamellae louver, end caps and inline couplers are available as accessories. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps).


Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	HF [Electronic high-frequency]
Feed-through wiring	-
Product family code	TMS028 [TMS028]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	36 W
Connection	-
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable
Product Data	
Order product name	TMS028 2xTL-D36W HF
Full product name	TMS028 2xTL-D36W HF
Full product code	871829104495600
Order code	910925850403
Material Nr. (12NC)	910925850403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291044956
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291044956

TMS028

Dimensional drawing



Product
TMS028 2xTL-D36W HF

