



GentleSpace gen2

BY471P GRN170S/840 PSD A50 G MBW SI SWP

GentleSpace 2, LED GreenLine system flux 17000 lm, 840 neutral white, Power supply unit with DALI interface, Asymmetrical mirror axis angle 50°, Glass, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

General Information			
Lamp family code	GRN170S [LED GreenLine system flux 17000 lm]	Service tag	Yes
Cap-Base	- [-]	Product family code	BY471P [GentleSpace 2]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Embedded control	-
Gear	EB [Electronic]	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on easily flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	17,000 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	155 lm/W

GentleSpace gen2

Color rendering index (CRI)	≥80
Number of light sources	12
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Asymmetrical mirror axis angle 50°
Optical cover type	Glass
Luminaire light beam spread	56° x 33°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	110 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Clear
Overall length	600 mm
Overall width	450 mm
Overall height	150 mm

Dimensions (Height x Width x Depth)	150 x 450 x 600 mm
-------------------------------------	--------------------

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	BY471P GRN170S/840 PSD A50 G MBW SI SWP
Full product name	BY471P GRN170S/840 PSD A50 G MBW SI SWP
Full product code	871869634595500
Order code	34595500
Material Nr. (12NC)	910925863182
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696345955
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696345955

GentleSpace gen2

Dimensional drawing

