



CoreLine recessed

RC120B LED27S/840 PSD W60L60

Coreline Recessed, LED Module, system flux 2700 lm, 840 neutral white, Power supply unit with DALI interface

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information			
Lamp family code	LED27S [LED Module, system flux 2700 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Product family code	RC120B [Coreline Recessed]
Light source replaceable	No	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Performance
Gear	EB [Electronic]	CE mark	Yes
Driver included	Yes	Warranty period	3 years + 2 years upon registration
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 30 s
		EU RoHS compliant	Yes

CoreLine recessed

Light Technical	
Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	92 lm/W
Color rendering index (CRI)	≥80
Number of light sources	2
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Polycarbonate linear satinized
Luminaire light beam spread	86°
Unified glare rating CEN	Not applicable

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	14.7 A
Inrush time	0.25 ms
Power Consumption	26.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	38

Temperature	
Ambient temperature range	+10 to +40 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing Material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White

Optical cover finish	Textured
Overall length	597 mm
Overall width	597 mm
Overall height	32 mm
Dimensions (Height x Width x Depth)	32 x 597 x 597 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data	
Order product name	RC120B LED27S/840 PSD W60L60
Full product name	RC120B LED27S/840 PSD W60L60
Full product code	871829126819200
Order code	26819200
Material Nr. (12NC)	910925863273
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291268192
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291268192

CoreLine recessed

Dimensional drawing

