



DigiStreet

BGP760 LED44-/740 I DW50 DGR 32-48

DigiStreet Micro, LED module 4400 lm, 740 neutral white, Safety class I, Distribution wide 50, Dark grey, Spigot for diameter 32 to 48 mm

Developed with the aim of becoming your long-term partner,, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. Digistreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Lamp family code	LED44 [LED module 4400 lm]		
Light source replaceable	Yes		
Number of gear units	Unit		
Gear	EB [Electronic]		
Driver included	Yes		
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for		
		Light source engine type	LED
		Product family code	BGP760 [DigiStreet Micro]
		Lighting Technology	LED
		Value ladder	Specification
		CE mark	Yes

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Upwards light output ratio	0
Luminous Flux	3,784 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	146 lm/W
Colour rendering index (CRI)	70
Number of light sources	1
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	152° - 24° x 66°
Optic type outdoor	Distribution wide 50

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.225 ms
Power Consumption	26 W
Power Factor (Fraction)	0.97
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Housing Colour	Dark grey

Mounting device	Spigot for diameter 32 to 48 mm
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	695 mm
Overall width	236 mm
Overall height	103 mm
Effective projected area	0.0578 m²
Dimensions (height x width x depth)	103 x 236 x 695 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38. 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L97

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP760 LED44-/740 I DW50 DGR 32-48
Full product name	BGP760 LED44-/740 I DW50 DGR 32-48
Full EOC	871869637691100
Order code	37691100
Material no. (12 NC)	910925863566
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696376911
Numerator – packs per outer box	1
EAN/UPC – Case	8718696376911

Dimensional drawing

