



# DigiStreet

## BGP761 LED79-/830 II DM70 DGR DDF27 D18

DigiStreet Mini, LED module 7900 lm, 830 warm white, Safety class II, Distribution medium 70, Dark gray, Spigot for diameter 60 mm

Developed with the aim to become your long term partner „ the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the Philips CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire’s lifetime. Digistreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

### Product data

General Information			
Lamp family code	LED79 [LED module 7900 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Light source engine type	LED
Number of gear units	1 unit	Product family code	BGP761 [DigiStreet Mini]
Gear	EB [Electronic]	Lighting Technology	LED
Driver included	Yes	Value ladder	Specification
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s

EU RoHS compliant	Yes
-------------------	-----

#### Light Technical

Upward light output ratio	0
Luminous Flux	7,040 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium 70

#### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	59 W
Power Factor (Fraction)	0.98
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	11

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 60 mm

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	860 mm
Overall width	236 mm
Overall height	107 mm
Effective projected area	0.0666 m²
Dimensions (Height x Width x Depth)	107 x 236 x 860 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L92

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	50%

#### Product Data

Order product name	BGP761 LED79-/830 II DM70 DGR DDF27 D18
Full product name	BGP761 LED79-/830 II DM70 DGR DDF27 D18
Full product code	871869637700000
Order code	910925863575
Material Nr. (12NC)	910925863575
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696377000
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696377000

Dimensional drawing

