



DigiStreet

BGP762 LED139-/830 II DM11 DGR D9 62

DigiStreet Medium, LED module 13900 lm, 830 warm white, Safety class II, Distribution medium 31, Dark gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Spigot for diameter 60 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		
Lamp family code	LED139 [LED module 13900 lm]	
Light source replaceable	No	
Number of gear units	1 unit	
Gear	EB [Electronic]	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Light source engine type		LED
Product family code		BGP762 [DigiStreet Medium]
Lighting Technology		LED
Value ladder		Specification
CE mark		Yes
Warranty period		5 years
Flammability mark		-

ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	12,600 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	124 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium 31

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	102 W
Power Factor (Fraction)	0.99
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Driver/power unit/transformer	Power supply unit with DynaDimmer
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel

Housing Color	Dark gray
Mounting device	Spigot for diameter 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	860 mm
Overall width	361 mm
Overall height	107 mm
Effective projected area	0.068 m²
Dimensions (Height x Width x Depth)	107 x 361 x 860 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life	10 %
life 100000 h	
Lumen maintenance at median useful life*	L92
100000 h	

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP762 LED139-/830 II DM11 DGR D9 62
Full product name	BGP762 LED139-/830 II DM11 DGR D9 62
Full product code	871869637829800
Order code	37829800
Material Nr. (12NC)	910925863706
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696378298
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696378298

Dimensional drawing

