



# Pacific LED gen4

## WT470C LED64S/840 PSD WB ELD3 L1600

PACIFIC LED WATERPROOF, 840 neutral white, Power supply unit with DALI interface, Wide beam, Screw connection with plug and socket

PacificLED gen4 is a highly efficient and reliable LED waterproof luminaire that offers an excellent quality of light, with a uniform light distribution without visible striping or colour artefacts. The range offers modular construction to enable ease of upgrade and maintenance. The new optical system provides distortion-free lighting with improved visual guidance, which makes it ideally suited to general industry, warehouses and parking areas. The range also offers the option of multiple optics to ensure an optimised lighting scheme for a wide range of applications. For industrial applications, PacificLED gen4 offers an open product architecture with tool-less access to the gear tray and an innovative end-cap design with built-in connector for fast and easy installation. The single-piece mounting clamp ensures no small, loose components that could affect the primary production process.

### Product data

General Information			
Light source replaceable	Yes		useful life (B50) value also represents the B10 value.
Number of gear units	Unit	Product family code	WT470C [PACIFIC LED WATERPROOF]
Driver included	Yes	Lighting Technology	LED
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on easily flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s

# Pacific LED gen4

EU RoHS compliant	Yes
<b>Light Technical</b>	
Luminous Flux	6,500 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	129 lm/W
Colour rendering index (CRI)	>80
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	110° x 110°
Unified Glare Rating (CEN)	22
<b>Operating and Electrical</b>	
Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.28 ms
Power Consumption	50.5 W
Power Factor (Fraction)	0.98
Connection	Screw connection with plug and socket
Cable	–
Number of products on MCB of 16 A type B	24
<b>Temperature</b>	
Ambient temperature range	0 to +30 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
<b>Mechanical and Housing</b>	
Housing material	Polycarbonate
Reflector material	–
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White

Optical cover/lens finish	Clear
Overall length	1,621 mm
Overall width	96 mm
Overall height	108 mm
Dimensions (height x width x depth)	108 x 96 x 1621 mm
<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable
<b>Product Data</b>	
Order product name	WT470C LED64S/840 PSD WB ELD3 L1600
Full product name	WT470C LED64S/840 PSD WB ELD3 L1600
Full EOC	871869637993600
Order code	37993600
Material no. (12 NC)	910925863871
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696379936
Numerator – packs per outer box	1
EAN/UPC – Case	8718696379936

## Pacific LED gen4

### Dimensional drawing

