



# Pacific LED gen4

## WT480X LED64S/840 WB ACW TW3 L1600

Pacific LED Circular Economy Green, 840 neutral white, Wide beam, Screw connection with plug and socket

PacificLED gen4 is a highly efficient and reliable LED waterproof luminaire that offers an excellent quality of light, with a uniform light distribution without visible striping or colour artefacts. The range offers modular construction to enable ease of upgrade and maintenance. The new optical system provides distortion-free lighting with improved visual guidance, which makes it ideally suited to general industry, warehouses and parking areas. The range also offers the option of multiple optics to ensure an optimised lighting scheme for a wide range of applications. For industrial applications, PacificLED gen4 offers an open product architecture with tool-less access to the gear tray and an innovative end-cap design with built-in connector for fast and easy installation. The single-piece mounting clamp ensures no small, loose components that could affect the primary production process.

### Product data

General Information	
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.

Product family code	WT480X [Pacific LED Circular Economy Green]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes

# Pacific LED gen4

Light Technical	
Luminous Flux	6,500 lm
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	138 lm/W
Colour rendering index (CRI)	>80
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	110° x 110°
Unified Glare Rating (CEN)	22

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.5 A
Inrush time	1 ms
Power Consumption	47 W
Power Factor (Fraction)	0.98
Connection	Screw connection with plug and socket
Cable	-
Number of products on MCB of 16 A type B	18

Temperature	
Ambient temperature range	-30 to +45 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,642 mm

Overall width	96 mm
Overall height	108 mm
Dimensions (height x width x depth)	108 x 96 x 1642 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L70

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

Product Data	
Order product name	WT480X LED64S/840 WB ACW TW3 L1600
Full product name	WT480X LED64S/840 WB ACW TW3 L1600
Full EOC	871869638054300
Order code	38054300
Material no. (12 NC)	910925863933
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696380543
Numerator – packs per outer box	1
EAN/UPC - Case	8718696380543

## Pacific LED gen4

### Dimensional drawing

