



# CoreLine recessed

## RC135B LED27S/840 PSD W62L62 OC

CoreLine recessed, 22 W, 620x620 mm, 2700 lm, 4000 K, DALI, UGR19

Philips CoreLine recessed delivers on the CoreLine promise of innovative, easy-to-use, high-quality luminaires. It's a high-quality recessed LED that's designed to replace existing recessed luminaires with T8 or T5 technology. This CoreLine family also features an innovative new choice of multiple lumen outputs in one single luminaire, called MultiLumen. Instant energy savings and a longer lifetime, make this is an environmentally-friendly and cost-saving solution. With a quick-connector or Wieland feature, CoreLine RC136B recessed luminaires are quick and easy to install. Also available within the range are Interact Ready luminaires with integrated wireless communications, which are fully compatible with Interact gateways, sensors and software.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

### Product data

General Information			
Light source replaceable	No	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Number of gear units	1 unit		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen		
		Service tag	Yes
		Product family code	RC135B [Coreline Recessed]
		Lighting Technology	LED
		Value ladder	Performance
		CE mark	Yes

## CoreLine recessed

Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	123 lm/W
Color rendering index (CRI)	≥80
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	81° x 80°
Unified glare rating CEN	19

### Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	14.7 A
Inrush time	0.25 ms
Power Consumption	22 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	–
Number of products on MCB of 16 A type B	38

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate

Optical cover material	Polycarbonate
Fixation material	–
Housing Color	White
Optical cover finish	Textured
Overall length	622 mm
Overall width	622 mm
Overall height	41 mm
Dimensions (Height x Width x Depth)	41 x 622 x 622 mm

### Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	–
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-8%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	RC135B LED27S/840 PSD W62L62 OC
Full product name	RC135B LED27S/840 PSD W62L62 OC
Full product code	871869934846500
Order code	910925864805
Material Nr. (12NC)	910925864805
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699348465
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699348465

## CoreLine recessed

### Dimensional drawing

