



# CoreLine surface-mounted

## SM134V LED27S/840 PSD W60L60 ELB3 OC

CoreLine surface-mounted, 25.5 W, 600x600 mm, 2700 lm, 4000 K, DALI, UGR19, ELB3h

Philips CoreLine surface-mounted light fixtures deliver on the CoreLine promise of innovative, easy-to-use, high-quality luminaires. These high-quality LEDs are designed to replace existing surface-mounted luminaires with T8 or T5 technology. This CoreLine family also features an innovative new choice of multiple lumen outputs in one single luminaire, called MultiLumen. Instant energy savings and a longer lifetime, make this is an environmentally-friendly and cost-saving surface LED light solution. With a quick-connector feature, our SM136V surface-mounted luminaires are quick and easy to install. Also available within the range are Interact Ready luminaires with integrated wireless communications, which are fully compatible with Interact gateways, sensors and software.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

### Product data

General Information		Remarks
Light source replaceable	No	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example
Number of gear units	1 unit	
Driver included	Yes	

## CoreLine surface-mounted

	B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	SM134V [Coreline Surface]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	≥80
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	81°
Unified glare rating CEN	19

### Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	14.7 A
Inrush time	0.25 ms
Power Consumption	25.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	–
Number of products on MCB of 16 A type B	38

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
------------------	-------

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Textured
Overall length	600 mm
Overall width	600 mm
Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 600 x 600 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	–
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-8%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1% (no dimming in emergency mode)
Suitable for random switching	Yes

### Product Data

Order product name	SM134V LED27S/840 PSD W60L60 ELB3 OC
Full product name	SM134V LED27S/840 PSD W60L60 ELB3 OC
Full product code	871869934874800
Order code	910925864833
Material Nr. (12NC)	910925864833
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699348748
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699348748

CoreLine surface-mounted

Dimensional drawing

