



# Mini 300 LED gen2

BBP400 ECO121-3S/757 I A WH MSP D9 SNS C

Mini300 LED gen2, LED EconomyLine 12100 lm, Asymmetrical

With operating margins under pressure, companies are looking for ways to save energy. LED products like our Mini 300 LED gen2 luminaires are a perfect solution. Designed for petrol-station canopies and low-bay applications, these ultra-efficient retrofit fixtures offer outstanding light quality, effective thermal management, and a very long lifespan. Reduced maintenance, replacement and energy cost means a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money by opting for green products. A movement detector combined with a daylight sensor enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – for instance, reading status and managing lighting from the floor by laptop or Smartphone via Bluetooth.

## Product data

General Information		Light Technical	
Lamp family code	ECO121 [LED EconomyLine 12100 lm]	EU RoHS compliant	No
Light source replaceable	Yes	Embedded control	-
Number of gear units	1 unit		
Driver included	Yes	Upward light output ratio	0
Photocell	-	Luminous Flux	12,700 lm
Light source engine type	LED	Standard tilt angle posttop	0°
Product family code	BBP400 [Mini300 LED gen2]	Standard tilt angle side entry	0°
Lighting Technology	LED	Correlated Color Temperature (Nom)	5700 K
Glow-wire test	Temperature 960 °C, duration 5 s	Luminous Efficacy (rated) (Nom)	123 lm/W
Flammability mark	-	Color rendering index (CRI)	≥70
CE mark	Yes	Number of light sources	48
ENEC mark	ENEC mark	Light source color	757 cool white
Warranty period	5 years	Optical cover type	Flat glass

## Mini 300 LED gen2

Luminaire light beam spread	140° x 70°
Optic type outdoor	Asymmetrical

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	88 W
Power Factor (Fraction)	0.97
Connection	Screw connection block 5-pole
Cable	Cable 2.0 m with screw connector
Number of products on MCB of 16 A type B 8	

### Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	White
Mounting device	-
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	413 mm
Overall width	413 mm
Overall height	95 mm

Effective projected area	0 m²
Dimensions (Height x Width x Depth)	95 x 413 x 413 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.1 %
-------------------------------	-------


### Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

### Product Data

Order product name	BBP400 ECO121-3S/757 I A WH MSP D9 SNS C
Full product name	BBP400 ECO121-3S/757 I A WH MSP D9 SNS C
Full product code	871829187831500
Order code	910930205353
Material Nr. (12NC)	910930205353
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291878315
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291878315

## Dimensional drawing



## Mini 300 LED gen2

