



Mini 300 LED gen2

BCS400 ECO151-3S/757 I A WH MSP MDU MWS

Mini300 LED gen2, LED EconomyLine 15100 lm, Asymmetrical, Movement detection unit

The Mini 300 LED gen2 luminaires provides highly efficient, controlable and manageable lighting solutions for petrol station canopies and low bay applications. These ultra-efficient retrofit LED fixtures are the latest development of the Philips Mini 300 range offering outstanding light quality, effective thermal management, and long lifespan. Reduced maintenance, replacement and energy costs also mean a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money without compromising on light quality by opting for energy efficient LED products. The integrated movement detector, daylight sensor and scheduler options enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – reading status, managing and controlling lighting from ground level using a laptop or Smartphone via Bluetooth - removing the need for access cranes or ladders.

Product data

General Information		Warranty period	
Lamp family code	ECO151 [LED EconomyLine 15100 lm]	Flammability mark	-
Light source replaceable	Yes	ENEC mark	ENEC mark
Number of gear units	1 unit	Glow-wire test	Temperature 960 °C, duration 5 s
Driver included	Yes	EU RoHS compliant	No
Photocell	Photocell included	Light Technical	
Light source engine type	LED	Upward light output ratio	0
Product family code	BCS400 [Mini300 LED gen2]	Luminous Flux	15,800 lm
Lighting Technology	LED	Standard tilt angle posttop	0°
Embedded control	Movement detection unit	Standard tilt angle side entry	0°
CE mark	Yes		

Mini 300 LED gen2

Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	124 lm/W
Color rendering index (CRI)	≥70
Number of light sources	60
Light source color	757 cool white
Optical cover type	Flat glass
Luminaire light beam spread	140° x 70°
Optic type outdoor	Asymmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	108 W
Power Factor (Fraction)	0.98
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B 8	

Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	White
Mounting device	-
Optical cover shape	Convex lens
Optical cover finish	Clear

Overall length	374 mm
Overall width	374 mm
Overall height	152 mm
Effective projected area	0 m²
Dimensions (Height x Width x Depth)	152 x 374 x 374 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.1 %
-------------------------------	-------

Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BCS400 ECO151-3S/757 I A WH MSP MDU MWS
Full product name	BCS400 ECO151-3S/757 I A WH MSP MDU MWS
Full product code	871829189312700
Order code	910930205406
Material Nr. (12NC)	910930205406
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291893127
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291893127

Mini 300 LED gen2

Dimensional drawing

