



Mini 300 LED gen2

BCS400 ECO151-3S/757 II PRM SI MDU MWS P

Mini300 LED gen2, LED EconomyLine 15100 lm, Petrol rotational symmetric medium, Movement detection unit

With operating margins under pressure, companies are looking for ways to save energy. LED products like our Mini 300 LED gen2 luminaires are a perfect solution. Designed for petrol-station canopies and low-bay applications, these ultra-efficient retrofit fixtures offer outstanding light quality, effective thermal management, and a very long lifespan. Reduced maintenance, replacement and energy cost means a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money by opting for green products. A movement detector combined with a daylight sensor enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – for instance, reading status and managing lighting from the floor by laptop or Smartphone via Bluetooth.

Product data

General Information		Light Technical	
Lamp family code	ECO151 [LED EconomyLine 15100 lm]	Upward light output ratio	0
Light source replaceable	Yes	Luminous Flux	15,800 lm
Number of gear units	1 unit	Standard tilt angle posttop	0°
Driver included	Yes	Standard tilt angle side entry	0°
Photocell	Photocell included	Correlated Color Temperature (Nom)	5700 K
Light source engine type	LED	Luminous Efficacy (rated) (Nom)	124 lm/W
Product family code	BCS400 [Mini300 LED gen2]		
Lighting Technology	LED		
Embedded control	Movement detection unit		
CE mark	Yes		
Warranty period	5 years		
Flammability mark	-		
ENEC mark	ENEC mark		
Glow-wire test	Temperature 960 °C, duration 5 s		
EU RoHS compliant	No		

Mini 300 LED gen2

Color rendering index (CRI)	≥70
Number of light sources	60
Light source color	757 cool white
Optical cover type	Flat glass
Luminaire light beam spread	114°
Optic type outdoor	Petrol rotational symmetric medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	108 W
Power Factor (Fraction)	0.98
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B 8	

Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Mounting device	Suspension set simple, standard
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	374 mm

Overall width	374 mm
Overall height	152 mm
Effective projected area	0 m²
Dimensions (Height x Width x Depth)	152 x 374 x 374 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.1 %
-------------------------------	-------

Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BCS400 ECO151-3S/757 II PRM SI MDU MWS P
Full product name	BCS400 ECO151-3S/757 II PRM SI MDU MWS P
Full product code	871829189322600
Order code	89322600
Material Nr. (12NC)	910930205407
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291893226
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291893226

Dimensional drawing



Mini 300 LED gen2

