



Mini 300 LED gen2

BCS400 GRN88-3S/740 II PRM WH MDU MWS

Mini300 LED gen2, LED GreenLine 8800 lm, Petrol rotational symmetric medium, Movement detection unit

With operating margins under pressure, companies are looking for ways to save energy. LED products like our Mini 300 LED gen2 luminaires are a perfect solution. Designed for petrol-station canopies and low-bay applications, these ultra-efficient retrofit fixtures offer outstanding light quality, effective thermal management, and a very long lifespan. Reduced maintenance, replacement and energy cost means a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money by opting for green products. A movement detector combined with a daylight sensor enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – for instance, reading status and managing lighting from the floor by laptop or Smartphone via Bluetooth.

Product data

General Information	
Lamp family code	GRN88 [LED GreenLine 8800 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Photocell	-
Light source engine type	LED
Product family code	BCS400 [Mini300 LED gen2]
Lighting Technology	LED
Glow-wire test	Temperature 960 °C, duration 5 s
Flammability mark	-
CE mark	Yes

ENEC mark	ENEC mark
Warranty period	5 years
EU RoHS compliant	No
Embedded control	Movement detection unit
Light Technical	
Upward light output ratio	0
Luminous Flux	9,200 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	137 lm/W

Mini 300 LED gen2

Color rendering index (CRI)	≥70
Number of light sources	64
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	114°
Optic type outdoor	Petrol rotational symmetric medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	67 W
Power Factor (Fraction)	0.9
Connection	Screw connection block 2-pole
Cable	-
Number of products on MCB of 16 A type B 8	

Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	White
Mounting device	-
Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	374 mm

Overall width	374 mm
Overall height	152 mm
Effective projected area	0 m²
Dimensions (Height x Width x Depth)	152 x 374 x 374 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.1 %
-------------------------------	-------

Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BCS400 GRN88-3S/740 II PRM WH MDU MWS
Full product name	BCS400 GRN88-3S/740 II PRM WH MDU MWS
Full product code	871829190948400
Order code	910930205452
Material Nr. (12NC)	910930205452
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291909484
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291909484

Dimensional drawing



Mini 300 LED gen2

