



# Mini 300 LED gen2

## BVS400 ECO75-3S/757 I DM WH

Mini300 LED gen2, 32, LED EconomyLine 7500 lm, LED, 54 W, Power supply unit regulating, Distribution medium, Flat glass, 140° x 70°

With operating margins under pressure, companies are looking for ways to save energy. LED products like our Mini 300 LED gen2 luminaires are a perfect solution. Designed for petrol-station canopies and low-bay applications, these ultra-efficient retrofit fixtures offer outstanding light quality, effective thermal management, and a very long lifespan. Reduced maintenance, replacement and energy cost means a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money by opting for green products. A movement detector combined with a daylight sensor enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – for instance, reading status and managing lighting from the floor by laptop or Smartphone via Bluetooth.

### Product data

General Information	
Lamp family code	ECO75 [LED EconomyLine 7500 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Photocell	-
Light source engine type	LED
Product family code	BVS400 [Mini300 LED gen2]
Lighting Technology	LED
Embedded control	-
CE mark	Yes

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 960 °C, duration 5 s
EU RoHS compliant	No
Light Technical	
Upward light output ratio	0
Luminous Flux	7,900 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°

Mini 300 LED gen2

Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	123 lm/W
Color rendering index (CRI)	≥70
Number of light sources	32
Light source color	757 cool white
Optical cover type	Flat glass
Luminaire light beam spread	140° x 70°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	54 W
Power Factor (Fraction)	0.97
Connection	Screw connection block 3-pole
Cable	Cable 0.45 m with connector 3-pole
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	White
Mounting device	-

Optical cover shape	Convex lens
Optical cover finish	Clear
Overall length	440 mm
Overall width	374 mm
Overall height	96 mm
Effective projected area	0 m²
Dimensions (Height x Width x Depth)	96 x 374 x 440 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2


Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.1 %
-------------------------------	-------

Product Data

Order product name	BVS400 ECO75-3S/757 I DM WH
Full product name	BVS400 ECO75-3S/757 I DM WH
Full product code	871829106727600
Order code	06727600
Material Nr. (12NC)	910930205468
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291067276
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291067276

Dimensional drawing



## Mini 300 LED gen2

