



# Mini 300 LED gen2

## BCS400 GRN94-3S/757 I PAM WH

Mini300 LED gen2, 64, LED GreenLine 9400 lm, LED, 65 W, Power supply unit regulating, Petrol asymmetric medium, Flat glass, 104° x 98°

With operating margins under pressure, companies are looking for ways to save energy. LED products like our Mini 300 LED gen2 luminaires are a perfect solution. Designed for petrol-station canopies and low-bay applications, these ultra-efficient retrofit fixtures offer outstanding light quality, effective thermal management, and a very long lifespan. Reduced maintenance, replacement and energy cost means a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money by opting for green products. A movement detector combined with a daylight sensor enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – for instance, reading status and managing lighting from the floor by laptop or Smartphone via Bluetooth.

### Product data

| General Information      |                               |                                |                                  |
|--------------------------|-------------------------------|--------------------------------|----------------------------------|
| Lamp family code         | GRN94 [LED GreenLine 9400 lm] | Warranty period                | 5 years                          |
| Light source replaceable | Yes                           | Flammability mark              | -                                |
| Number of gear units     | 1 unit                        | ENEC mark                      | ENEC mark                        |
| Driver included          | Yes                           | Glow-wire test                 | Temperature 960 °C, duration 5 s |
| Photocell                | -                             | EU RoHS compliant              | No                               |
| Light source engine type | LED                           | Light Technical                |                                  |
| Product family code      | BCS400 [Mini300 LED gen2]     | Upward light output ratio      | 0                                |
| Lighting Technology      | LED                           | Luminous Flux                  | 9,900 lm                         |
| Embedded control         | -                             | Standard tilt angle posttop    | 0°                               |
| CE mark                  | Yes                           | Standard tilt angle side entry | 0°                               |

Mini 300 LED gen2

|                                    |                          |
|------------------------------------|--------------------------|
| Correlated Color Temperature (Nom) | 5700 K                   |
| Luminous Efficacy (rated) (Nom)    | 138 lm/W                 |
| Color rendering index (CRI)        | ≥70                      |
| Number of light sources            | 64                       |
| Light source color                 | 757 cool white           |
| Optical cover type                 | Flat glass               |
| Luminaire light beam spread        | 104° x 98°               |
| Optic type outdoor                 | Petrol asymmetric medium |

Operating and Electrical

|  |                               |
|--|-------------------------------|
| Input Voltage                            | 220 to 240 V                  |
| Line Frequency                           | 50 to 60 Hz                   |
| Inrush current                           | 53 A                          |
| Inrush time                              | 0.3 ms                        |
| Power Consumption                        | 65 W                          |
| Power Factor (Fraction)                  | 0.96                          |
| Connection                               | Screw connection block 3-pole |
| Cable                                    | -                             |
| Number of products on MCB of 16 A type B | 8                             |

Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -30 to +40 °C |
|---------------------------|---------------|

Controls and Dimming

|                               |                              |
|-------------------------------|------------------------------|
| Dimmable                      | No                           |
| Driver/power unit/transformer | Power supply unit regulating |
| Constant light output         | No                           |

Mechanical and Housing

|                        |          |
|------------------------|----------|
| Housing Material       | Aluminum |
| Reflector material     | -        |
| Optic material         | Acrylate |
| Optical cover material | Glass    |
| Fixation material      | Aluminum |
| Housing Color          | White    |
| Mounting device        | -        |

|                                     |                    |
|-------------------------------------|--------------------|
| Optical cover shape                 | Convex lens        |
| Optical cover finish                | Clear              |
| Overall length                      | 374 mm             |
| Overall width                       | 374 mm             |
| Overall height                      | 152 mm             |
| Effective projected area            | 0 m²               |
| Dimensions (Height x Width x Depth) | 152 x 374 x 374 mm |

Approval and Application

|  |  |
|--|--|
| Ingress protection code                | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code           | IK08 [5 J vandal-protected]                  |
| Surge Protection (Common/Differential) | Philips standard surge protection level      |
| Protection class IEC                   | Safety class I                               |

Initial Performance (IEC Compliant)

|                                       |                        |
|---------------------------------------|------------------------|
| Luminous flux tolerance               | +/-7%                  |
| Initial chromaticity                  | (0.341, 0.329) SDCM <5 |
| Power consumption tolerance           | +/-10%                 |
| Init. Color Rendering Index Tolerance | +/-2                   |

Over Time Performance (IEC Compliant)

|                               |       |
|-------------------------------|-------|
| Driver failure rate at 5000 h | 0.1 % |
|-------------------------------|-------|

Product Data

|                                 |                              |
|---------------------------------|------------------------------|
| Order product name              | BCS400 GRN94-3S/757 I PAM WH |
| Full product name               | BCS400 GRN94-3S/757 I PAM WH |
| Full product code               | 871829106845700              |
| Order code                      | 06845700                     |
| Material Nr. (12NC)             | 910930205587                 |
| Numerator - Quantity Per Pack   | 1                            |
| EAN/UPC - Product/Case          | 8718291068457                |
| Numerator - Packs per outer box | 1                            |
| EAN/UPC - Case                  | 8718291068457                |

Dimensional drawing



## Mini 300 LED gen2

