



Mini 300 LED gen2

BCS400 ECO75-3S/757 I PAM WH MDU PH

Mini300 LED gen2, LED EconomyLine 7500 lm, Petrol asymmetric medium, Movement detection unit

With operating margins under pressure, companies are looking for ways to save energy. LED products like our Mini 300 LED gen2 luminaires are a perfect solution. Designed for petrol-station canopies and low-bay applications, these ultra-efficient retrofit fixtures offer outstanding light quality, effective thermal management, and a very long lifespan. Reduced maintenance, replacement and energy cost means a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money by opting for green products. A movement detector combined with a daylight sensor enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – for instance, reading status and managing lighting from the floor by laptop or Smartphone via Bluetooth.

Product data

General Information		Light Technical	
Lamp family code	ECO75 [LED EconomyLine 7500 lm]	Upward light output ratio	0
Light source replaceable	Yes	Luminous Flux	7,900 lm
Number of gear units	1 unit	Standard tilt angle posttop	0°
Driver included	Yes	Standard tilt angle side entry	0°
Photocell	Photocell included	Correlated Color Temperature (Nom)	5700 K
Light source engine type	LED	Luminous Efficacy (rated) (Nom)	123 lm/W
Product family code	BCS400 [Mini300 LED gen2]		
Lighting Technology	LED		
Glow-wire test	Temperature 960 °C, duration 5 s		
Flammability mark	-		
CE mark	Yes		
ENEC mark	ENEC mark		
Warranty period	5 years		
EU RoHS compliant	No		
Embedded control	Movement detection unit		

Mini 300 LED gen2

Color rendering index (CRI)	≥70
Number of light sources	32
Light source color	757 cool white
Optical cover type	Flat glass
Luminaire light beam spread	104° x 98°
Optic type outdoor	Petrol asymmetric medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	54 W
Power Factor (Fraction)	0.97
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	White
Mounting device	-
Optical cover shape	Convex lens
Optical cover finish	Clear

Overall length	374 mm
Overall width	374 mm
Overall height	152 mm
Effective projected area	0 m²
Dimensions (Height x Width x Depth)	152 x 374 x 374 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.1 %
-------------------------------	-------

Application Conditions

Maximum dim level	10%
-------------------	-----

Product Data

Order product name	BCS400 ECO75-3S/757 I PAM WH MDU PH
Full product name	BCS400 ECO75-3S/757 I PAM WH MDU PH
Full product code	871829189116100
Order code	910930205646
Material Nr. (12NC)	910930205646
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291891161
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291891161

Dimensional drawing



Mini 300 LED gen2

