



GentleSpace gen2

BY470P GRN130S/840 PSD-CLO WB GC SI

GentleSpace 2, LED GreenLine system flux 13000 lm, 840 neutral white, Power supply unit with DALI interface and constant light output, Wide beam, Clear glass, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips continues to improve even further: an improved total cost of ownership, even in extreme conditions with the the GS-2 Xtreme version, which can be used up to +60 °C or 100,000 hrs of lifetime (L80), both ensured by an integrated over-heat protection. In addition, a wide variety of options – e.g. optics, coatings, mounting possibilities, cover materials and suitable for explosive zones 2/22 – are available to ensure an ideal solution for your application. Additionally, the GentleSpace gen2 can be equipped for use in a central emergency grid (PSED).

Product data

General Information			
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
Cap-Base	- [-]	Service tag	Yes
Light source replaceable	Yes	Product family code	BY470P [GentleSpace 2]
Number of gear units	1 unit	Lighting Technology	LED
Gear	EB [Electronic]	Glow-wire test	Temperature 850 °C, duration 5 s
Driver included	Yes	Flammability mark	For mounting on easily flammable surfaces
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	Yes

GentleSpace gen2

Embedded control	-
------------------	---

Light Technical	
Luminous Flux	13,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	149 lm/W
Color rendering index (CRI)	≥80
Number of light sources	8
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Clear glass
Luminaire light beam spread	42° x 44°
Unified glare rating CEN	25

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	70 W
Average CLO power consumption	78 W
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	87 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

Temperature	
Ambient temperature range	-30 to +45 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface and constant light output
Control interface	DALI
Constant light output	Programmable

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass

Fixation material	Stainless steel
Housing Color	Silver
Optical cover finish	Clear
Overall length	450 mm
Overall width	350 mm
Overall height	130 mm
Dimensions (Height x Width x Depth)	130 x 350 x 450 mm

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

Product Data	
Order product name	BY470P GRN130S/840 PSD-CLO WB GC SI
Full product name	BY470P GRN130S/840 PSD-CLO WB GC SI
Full product code	871869632256700
Order code	910930206016
Material Nr. (12NC)	910930206016
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696322567
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696322567

GentleSpace gen2

Dimensional drawing

