



GentleSpace gen2

BY470P GRN130S/840 PSD-CLO WB GC BR SI S

GentleSpace 2, LED GreenLine system flux 13000 lm, 840 neutral white, Power supply unit with DALI interface and constant light output, Wide beam, Silver, Swimming pool protected coating

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

General Information			
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Service tag	Yes
Light source replaceable	Yes	Product family code	BY470P [GentleSpace 2]
Number of gear units	1 unit	Lighting Technology	LED
Gear	EB [Electronic]	Embedded control	-
Driver included	Yes	CE mark	Yes
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Warranty period	5 years
		Flammability mark	For mounting on easily flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes

GentleSpace gen2

Light Technical	
Luminous Flux	13,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	149 lm/W
Color rendering index (CRI)	≥80
Number of light sources	8
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Clear glass
Luminaire light beam spread	42° x 44°
Unified glare rating CEN	25
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	70 W
Average CLO power consumption	78 W
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	87 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12
Temperature	
Ambient temperature range	-30 to +45 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface and constant light output
Control interface	DALI
Constant light output	Programmable
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Silver

Optical cover finish	Clear
Overall length	450 mm
Overall width	350 mm
Overall height	130 mm
Dimensions (Height x Width x Depth)	130 x 350 x 450 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No
Product Data	
Order product name	BY470P GRN130S/840 PSD-CLO WB GC BR SI S
Full product name	BY470P GRN130S/840 PSD-CLO WB GC BR SI S
Full product code	871869632296300
Order code	32296300
Material Nr. (12NC)	910930206056
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696322963
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696322963

GentleSpace gen2

Dimensional drawing

